



Priyal Propack's vibro sifter is used for the efficient separation and grading of powdered or granular materials. It employs vibration and sieving screens to remove impurities and achieve particle size classification. Vibro sifters offer high throughput, accurate sieving, and easy operation in pharmaceutical manufacturing. They ensure product quality, consistency, and compliance with regulatory standards. Vibro sifters are essential for efficient material screening and quality control in the pharmaceutical industry.



SALIENT FEATURES

- **GMP Compliance:** Designed in adherence to Good Manufacturing Practice standards for pharmaceutical hygiene and safety.
- **Tool-Free Assembly:** Facilitates quick and efficient cleaning, maintenance, and batch changeovers.
- **Stainless Steel Contact Parts:** Corrosion-resistant construction ensures product integrity and easy cleaning.
- **Vibration Control:** Allows operators to adjust vibration intensity and frequency for optimal sieving.
- **Dust-Free Operation:** Equipped with dust-tight covers and seals to prevent particle escape, maintaining a clean and sterile environment.

TECHNICAL SPECIFICATION

Model	PPVS 20	PPVS 30	PPVS 36	PPVS 48	PPVS 60	PPVS 72
SCREEN DIA.	500 MM.	750 MM.	900 MM.	1200 MM.	1500 MM.	1800 MM.
CAPACITY/HOUR*	25 TO 100 KGS.	30 TO 200 KGS.	30 TO 300 KGS.	50 TO 500 KGS.	100 TO 700 KGS.	100 TO 1000 KGS.
CHARGING HEIGHT	1200 MM WITHOUT LID	1050 MM WITHOUT LID	1050 MM WITHOUT LID	1050 MM WITHOUT LID	1050 MM WITHOUT LID	1050 MM WITHOUT LID
DISCHARGING HEIGHT	720 MM.	670 MM.	670 MM.	670 MM.	670 MM.	670 MM.
MAIN ELECTRIC MOTOR	0.50 HP/1440 RPM/3 PH	1.0 HP/1440 RPM/3 PH	1.5 HP/1440 RPM/3 PH	1 HP (HEAVY DUTY)	2 HP (HEAVY DUTY)	3 HP (HEAVY DUTY)

Contact Us...

Contact No. +91 7303379696 / +91 8879660789

Email: connect@priyalpropack.com / priyalpropack@gmail.com

Website: www.priyalpropack.com

Office Address: PAP-R-532, T.T.C Industrial Area, Rabale MIDC, Navi Mumbai – 400701. Maharashtra.